


AQUA-SENSE[®]

Microincision IOL

with
ADAPTIV[™]
OPTICS



Aqua SI
&
Aqua SIY



Small Incision IOLs

The clarity and range of aspheric Adaptiv™ Optics, now designed with minimized optic mass

Aqua SI



Overall Diameter:	13.0 mm
Optic Diameter:	6.0 mm
Minimum Incision:	1.8 mm
A-Constant*:	119.0 mm
Refractive Index:	1.46
AC-Depth*:	5.6
Angulation:	Step Vaulted
Lens Spherical Aberration	-0.12
Power Range: (in 0.5D increments)	4.0 to 34.0D

Aqua SIY



Small Incision

- Enhanced optic edge minimizes lens mass for small incision sizes.

Easier Folding

- Optic mass is distributed toward posterior side of the lens

Adaptiv™ Optics

- Aspheric optics designed for excellent image quality and contrast sensitivity

Predictable and Stable Refractive Outcomes

- With Aaren's exclusive Adaptiv Optic design, consistent results may be expected, even in cases of clinically occurring lens decentration or tilt
- Haptics are designed for maximum post-operative stability

Reduced Risk of PCO

- 360° double square edge optic design offers a formidable barrier against cell migration